

## VertiKlean® & VertiKlean® Max Mop head frames

Autoclavable QuickConnect<sup>™</sup> frames for VertiKlean<sup>®</sup> and VertiKlean<sup>®</sup> MAX<sup>™</sup> mops

## **Description**

The autoclavable frames for Contec's VertiKlean and VertiKlean MAX mop heads have Contec's QuickConnect handle adapter which enables use with a wide variety of telescoping and fixed length handles. The aluminum and stainless steel construction is lighteweight yet durable. All of the mop head frames listed may be sterilized by most common methods including gamma irradiation, ethylene oxide, or autoclave. Autoclavable at 121°C for 30 minutes.

## **Technical Information**

Part No.	Description	Material
2651A	Regular VK-Mop & VK-Max head frame, 7.5" x 1.75" x 4.25" / 19 x 4.7 x 11cm	Type 304 stainless steel; aluminum; Delrin®
2652A	Medium VK-Mop & VK-Max head frame, 11.5" x 1.75" x 4.25" / 29 x 4.7 x 11cm	Type 304 stainless steel; aluminum; Delrin®
2653A	Large VK-Mop & VK-Max head frame, 14" x 1.75" x 4.25" / 35.5 x 4.7 x 11cm	Type 304 stainless steel; aluminum; Delrin®







frame 2651A



frame 2652A



frame 2653A

## Notes:

- 1) Data shown are typical values and should not be used as product specifications.
- 2) The information presented here is applicable to the part numbers shown above, as well as to any product containing the same materials and produced under the same conditions, regardless of product size or packaging configuration. Please contact a Contec sales representative for more details.
  Revision date: 01/23/13

revision date. 01/23/13

